

	Excitation	Position	Fluorochromes	Filters	LP	
laser blu	488 nm	B	FITC	530/30	502	
		D	EMPTY			
		F	EMPTY			
		H	EMPTY			
		A	PERCP.CY5.5/BRILLIANT BLU 700	685/40		655
		C	SSC	488/10		
		E	EMPTY			
		G	EMPTY			
laser giallo verde	561 nm	B	PE-Cy5.5	710/50	685	
		D	PE	582/15		
		F	EMPTY			
		H	EMPTY			
		A	PE-Cy7	780/60		735
		C	PE-CF594	610/20		600
		E	EMPTY			
		G	EMPTY			
laser violetto	405 nm	B	BV711	710/50	690	
		D	BV605	610/20		595
		F	BV421/PACIFIC BLU/V450	450/50		
		H	EMPTY			
		A	BV785	780/60		750
		C	BV650	660/20		630
		E	BV510/AMCYAN/V500	525/50		505
		G	EMPTY			
laser rosso	640 nm	A	APC-Cy7/APC-H7	780-60	755	
		C	APC/ alexa 647	670/30		
		B	APC-Alexa 700/ R700/Alexa fluor 700	730/45		690
laser uv	640 nm	A	BUV 737	740/35	690	
		C	BUV 395	379/28		
		B	BUV 496	515/30		450