

	EXCITATION	POSITION	FLUOROCHROMES	BP FILTER	LP
BLU LASER	488 nm	B	FITC	530/30	502
		D	EMPTY		
		F	EMPTY		
		H	EMPTY		
		A	PERCP-CY5.5/BB700	685/40	655
		C	SSC	488/10	
		E	EMPTY		
		G	EMPTY		
YELLOW/GREEN LASER	561 nm	B	PE-CY5.5	710/50	685
		D	PE	585/15	
		F	EMPTY	780/60	735
		H	EMPTY		
		A	PE-CY7		
		C	PE-CF594		
		E	EMPTY	EMPTY	
		G	EMPTY		
VIOLET LASER	405 nm	B	BV711	710/50	690
		D	BV605	610/20	595
		F	BV421/V450/PACIFIC BLUE	450/50	750
		H	EMPTY		
		A	BV785	780/60	
		C	BV650	660/20	
		E	BV510/V500	525/50	505
		G	EMPTY		
RED LASER	640 nm	A	APC-CY7/APC-H7	780/60	755
		C	APC/ALEXA 647	670/60	690
		B	APC-ALEXA700/ALEXA FLUOR 700	730/45	
UV LASER	355 nm	A	BUV 737	740/35	690
		C	BUV 395	379/28	450
		B	BUV 496	515/30	