

	EXCITATION	POSITION	FLUOROCHROMES	BP FILTER	LP FILTER
BLU LASER	488 nm	B	PERCP-CY5.5/BB700	710/50	685
		D	PERCP-CY5.5/BB700	575/25	550
		F	SSC	488/10	
		H	EMPTY		
		A	PE-CY7	780/60	750
		C	PE-CF594	610/20	600
		E	FITC	530/30	505
		G	EMPTY		
VIOLET LASER	405 nm	B	BV711	710/50	685
		D	BV605	610/20	600
		F	BV421/V450/PACIFIC BLUE	450/50	
		H	EMPTY		
		A	BV785	780/60	750
		C	BV650	670/30	635
		E	BV510/V500	525/50	505
		G	EMPTY		
RED LASER	640 nm	A	APC-CY7/APC-H7	780/60	755
		C	APC/ALEXA 647	670/60	
		B	APC-ALEXA700/ALEXA FLUOR 700	730/45	690